PS20AC1

La legrand[®] designed to be better.

Industrial Extra Heavy-Duty Specification Grade Switch, Brown

PS20AC1



1pole Toggle Switch, Back & Side Wire, 20amp 120/277volt, Brown



features & benefits

- External screw-pressure-plate back and side wired. Accepts #14 #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of istallation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see <u>www.legrand.us/patents</u>.

specifications

General Info

Color: Brown Type: Toggle Duty: Extra Heavy Duty Number Of Poles: 1

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111 CSA Standard: Yes Federal Spec: Yes Fed Spec Number: WS896 UL Listing No: 20 UL Standard: Yes UN SPS C: 39121507

Dimensions

Depth U S: 1.073" Height U S: 3.281" Width U S: 1.320"

Technical Information

Amps: 20 Amp Volts: 120/277VAC Volts A C: 120/277 Grade Type: Industrial

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant