

# Extra Heavy-Duty Spec. Grade 347VAC Toggle Switch Back & Side Wire, White

PS371510W



Canadian 1pole Switch, Back & Side Wire,  
15amp 347volt, White



## features & benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: White  
Type: Toggle  
Duty: Extra Heavy Duty  
Number Of Poles: 1

### **Listing Agencies/Third Party Information**

CSA Listing Info: C22.2 111  
CSA Standard: Yes  
UN SPS C: 39121507

### **Dimensions**

Depth U S: 1.073"  
Height U S: 3.531"  
Width U S: 1.320"

### **Technical Information**

Amps: 15 Amp  
Volts: 347VAC  
Volts A C: 347  
Grade Type: Specification

### **Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant