

Extra Heavy-Duty Spec. 347VAC Toggle Switch Back & Side Wire, Ivory

PS372030I



Canadian 3way Switch, Back & Side Wire, 20amp 347volt, Ivory



features & benefits

- External screw-pressure-plate back and side wired. Accepts #14 #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Ivory Type: Toggle

Duty: Extra Heavy Duty Number Of Poles: 3-way

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111

CSA Standard: Yes UN SPS C: 39121507

Dimensions

Depth U S: 1.073" Height U S: 3.531" Width U S: 1.320"

Technical Information

Amps: 20 Amp Volts: 347VAC Volts A C: 347

Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant