

Industrial Extra Heavy-Duty Specification Grade Switch, White

PS15AC1W



1pole Toggle Switch, Back & Side Wire,
15amp 120/277volt, White



features & benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White
Type: Toggle
Duty: Extra Heavy Duty
Number Of Poles: 1

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111
CSA Standard: Yes
Federal Spec: Yes
Fed Spec Number: WS896
UL Listing No: 20
UL Standard: Yes
UN SPS C: 39121507

Dimensions

Depth U S: 1.073"
Height U S: 3.281"
Width U S: 1.320"

Technical Information

Amps: 15 Amp
Volts: 120/277VAC
Volts A C: 120/277
Grade Type: Industrial

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant