



POWER OUTLET RECEPTACLE OPENINGS, TWO GANG, BLACK

TP703BK | [Pass & Seymour](#)

FEATURES & BENEFITS

Two Gang Power Outlet Receptacle Opening, 2.1563" hole for 2.125" diameter device - 4 mtg. holes, Black Nylon.



- Molded of rugged, practically indestructible self-extinguishing nylon. ("TP" series only.)
- Available in "TP" series, extra 3/16 inch width and height than Standard size plates; and "TPJ" series, extra 3/16 inch width and height than Junior-Jumbo size plates.
- Available in Ivory, White, Brown, Gray, Black, Blue, Orange, Red, and Light Almond.
- Preferred for hospital, industrial, institutional, and other high-abuse applications.
- Nominal thickness, .070 inch.

SPECIFICATIONS

GENERAL INFO

Color: Black
Size: Standard
Special Features: Unbreakable

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: No
UL Listing No: No
UN SPSC: 39121704
UR: No

DIMENSIONS

Diameter (US): 2.1563" Hole

TECHNICAL INFORMATION

Material: Nylon

Capacity: 2-gang

COUNTRY OF ORIGIN

Country Of Origin: UNITED STATES OF AMERICA