

---

## 30 AMP NEMA L730 SINGLE RECEPTACLE

L730R | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Turnlok Single Receptacle, 3wire 30amp 277volt



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles  
Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Standard: Yes  
CUL Listing No: No  
cURus: No  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

## DIMENSIONS

Depth (US): 1.28"

Height (US): 3.28"

Width (US): 1.61"

## TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L1730

Volts: 277V

Volts (AC): 277

## COUNTRY OF ORIGIN

Country Of Origin: MEXICO