
MEDIUM BASE LAMPHOLDER

272 | [Pass & Seymour](#)



FEATURES & BENEFITS

Medium base, porcelain, one piece keyless. 2 terminals with tri-drive screws, fits 3 1/4" and 4" boxes, with cage neck.



- Quality Materials.
- Durability.
- Time-tested design.

SPECIFICATIONS

GENERAL INFO

Type: Incandescent Medium Base Lampholder

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: No
CUL Listing No: No
cURus: No
UL Listing No: Yes
UN SPSC: 39111803

DIMENSIONS

Diameter (US): 4.5"

TECHNICAL INFORMATION

Volts: 250V
Watts: 660

COUNTRY OF ORIGIN

Country Of Origin: CHINA