



SPECIFICATION GRADE QUAD RECEPTACLE, IVORY

4151 | [Pass & Seymour](#)

FEATURES & BENEFITS

Specification Grade Quad Receptacle, 15amp 125v, Ivory

- Rugged nylon face and body withstands impacts and hard use.
- Built-in wire stripping gauge.
- Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
- Heavy-duty, phosphor bronze contacts.
- Shielding walls guard against live-circuit-to-ground shorts.
- Split circuit break-off tabs.
- UL and CSA listed.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Ivory

Type: Quad Receptacles

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

Federal Spec: No

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Height (US): 4.5"

Width (US): 4.5"

TECHNICAL INFORMATION

Amps: 15A

Volts: 125V

Volts (AC): 125
Capacity: Quad
Grade Type: Specification

COUNTRY OF ORIGIN

Country Of Origin: MEXICO