

Specification Grade Decorator Switch, Gray

2603GRY



Three-way, Back and Side Wire, Decorator Switch, 15 amps, 120/277 volts, Gray.



features & benefits

- Impact-resistant polycarb back body and frame.
- Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
- Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.
- Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
- Terminals made of high conductivity brass and serrated for maximum wire gripping.
- Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
- Integral auto-ground clip for positive ground to metal boxes.
- Tri-drive ground, terminal, and mounting screws.
- All terminal screws backed out, ready-to-install.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Number Of Poles: 3-way
Style: Decorator

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 111

CSA Standard: Yes
UL Listing No: 20
UL Standard: Yes
UN SPS C: 39121507

Dimensions

Depth U S: 1.06"
Height U S: 3.531"
Width U S: 1.3"

Technical Information

Amps: 15 Amp
Volts: 120/277VAC
Volts A C: 120/277

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant