



SPECIFICATION GRADE DECORATOR SWITCH, BROWN

2623 | [Pass & Seymour](#)

FEATURES & BENEFITS

Three-way, Back and Side Wire, Decorator Switch, 20 amps, 120/277 volts, Brown.

- Impact-resistant polycarb back body and frame.
- Cushioned thermoplastic paddle assures smooth, quiet, long term operation.
- Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.
- Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.
- Terminals made of high conductivity brass and serrated for maximum wire gripping.
- Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.
- Integral auto-ground clip for positive ground to metal boxes.
- Tri-drive ground, terminal, and mounting screws.
- All terminal screws backed out, ready-to-install.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Number Of Poles: 3-way

Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

UL Listing No: 20

UL Standard: Yes

UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.06"

Height (US): 4.2"
Width (US): 1.3"

TECHNICAL INFORMATION

Amps: 20A
Volts: 120/277VAC
Volts (AC): 120/277

COUNTRY OF ORIGIN

Country Of Origin: MEXICO