

---

## TRADEMASTER GROUNDING TOGGLE SWITCH, BLACK

664BKG | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, Black.



- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Product Series: TradeMaster

Type: Toggle

Number Of Poles: 4-way

Special Features: Self-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 111

CSA Standard: Yes

UL Listing No: 20

UL Standard: Yes

UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.090"

Height (US): 3.281"  
Width (US): 1.25"

#### TECHNICAL INFORMATION

Amps: 15A  
Volts: 120VAC  
Volts (AC): 120

#### COUNTRY OF ORIGIN

Country Of Origin: MEXICO