
TRADEMASTER GROUNDING TOGGLE SWITCH, WHITE

664WG | [Pass & Seymour](#)



FEATURES & BENEFITS

Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, White.

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Product Series: TradeMaster

Type: Toggle

Number Of Poles: 4-way

Special Features: Self-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 111

CSA Standard: Yes

UL Listing No: 20

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.090"

Height (US): 3.281"

Width (US): 1.25"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120VAC

Volts (AC): 120

COUNTRY OF ORIGIN

Country Of Origin: MEXICO