

---

## MANUAL CONTROLLERS

7806P | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

#### NEMA 1 Nylon Enclosure with 1/2inch & 3/4inch Knockouts

High horsepower rating of 20HP. Compact design. Gull-wing shaped brass terminal pressure clamps. Constructed of glass-reinforced thermoplastic. Two-point contact arms. One-piece contact carrier. UL508 and cULus Listing of individual device and assembled device within enclosure. Heavy-duty zinc-plated steel strap. Two brass rivets secure strap to housing. External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals. Oversized silver alloy contacts. 2-3/4 inch hubs (7812-EX and 7813-EX). 2-1/2 inch knockouts on back and 2-1/2 inch -3/4 inch knockouts on top and bottom (7812-P, 7813-P, 7806-P). 2-1/2 inch knockouts on bottom and back (7832 and 7833).

---

### SPECIFICATIONS

#### GENERAL INFO

Type: NEMA 1 Nylon Enclosure  
Knockout Size: 1/2" & 3/4"

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UL Listing No: No  
UN SPSC: 39121507

#### DIMENSIONS

Weight: 0.46574