



HEAVY-DUTY DECORATOR SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 15A, 125V, BLACK

26252BK | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt Black



- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
 - One-piece, brass, triple-wipe power contacts for lasting retention.
 - Heavy-duty compact design for easier installation and long lasting performance.
 - Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
 - Impact-resistant nylon face.
 - Terminal compartments isolated from each other for positive conductor containment.
 - Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
 - All devices fit standard #26 opening wall plate.
 - Tri-drive terminal and mounting screws.
 - Auto-ground clip assures positive ground
 - For covering patents, see www.legrand.us/patents.
-
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Color: Black
Type: Receptacles
Duty: Heavy Duty
Special Features: Back,Side Wire
Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
cUL Standard: Yes
Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.833"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Specification

COUNTRY OF ORIGIN

Country Of Origin: MEXICO