IG26262W

La legrand[®] designed to be better.

Isolated Ground Heavy-Duty Decorator Spec Grade Receptacles, Back & Side Wire, 15A, 125V, White

IG26262W

Isolated Ground Heavy-Duty Decorator Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt White



features & benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.
- For covering patents, see <u>www.legrand.us/patents</u>.

specifications

General Info

Color: white Type: Receptacles Number Of Poles: 2 Number Of Wires: 3 Special Features: Isolated ground,back,side wire Style: Decorator

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No. 42 CSA Standard: Yes Federal Spec: Yes Fed Spec Number: WC596 UL Listing No: UL498 UL Standard: Yes UN SPS C: 39121406 UR: No

Dimensions

Depth U S: 0.833" Height U S: 3.281" Width U S: 1.322"

Technical Information

Amps: 15 Amp NEMA Configuration Number: 5-15R Volts: 125V Volts A C: 125 Capacity: Duplex Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO Buy American Act Status: Trade Agreement Act Compliant