



PLUGTAIL® EXTRA HEAVY-DUTY HOSPITAL GRADE TAMPER-RESISTANT RECEPTACLES, 20A, 125V, BROWN

PTTR63H | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Extra Heavy-Duty Hospital Grade Tamper-Resistant Duplex Receptacle 20amp 125volt Brown

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Extra heavy-duty 0.050" thick brass mounting strap for superior performance and durability.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Brown

Product Series: PlugTail

Type: Receptacles

Duty: Extra Heavy Duty

Special Features: Tamper-Resistant, Illuminated

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CUL Listing No: E140596
cULus: Yes
cUL Standard: UL498
Federal Spec: Yes
UL Listing No: E140596
UL Standard: UL498
UN SPSC: 39121406

DIMENSIONS

Depth (US): .866"
Height (US): 3.281"
Width (US): 1.625"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Hospital

COUNTRY OF ORIGIN

Country Of Origin: MEXICO