



HEAVY-DUTY HOSPITAL GRADE SINGLE RECEPTACLES, BACK & SIDE WIRE, 20A, 250V, WHITE

8801W | [Pass & Seymour](#)

FEATURES & BENEFITS

Heavy-Duty Hospital Grade Single Receptacle Back & Side Wire 20amp 250volt White



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Single Receptacles

Duty: Heavy Duty

Special Features: Back,Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

cUL Standard: Yes
cURus: No
Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.093"
Height (US): 3.28"
Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 20A
Volts: 250V
Volts (AC): 250
Capacity: Single
Grade Type: Hospital

COUNTRY OF ORIGIN

Country Of Origin: MEXICO