
WIDE SLIDE SERIES FAN SPEED CONTROL, IVORY

940841 | [Pass & Seymour](#)



FEATURES & BENEFITS

1.5amp Slide Dehummer Fan Control, Ivory

- Since the development of variable fan speed controls, many fans have made an annoying humming noise when their speed was reduced. Through the use of specially designed capacitive circuitry, these units can control fans at 3- or 4-speed levels in slide, rotary, and dual styles with virtually no fan motor noise.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Product Series: Wide Slide
Type: Wide Side
Number Of Poles: 1
Special Features: RFI Protected, De-Hummer

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121502
UR: No

DIMENSIONS

Depth (US): 1.469"
Height (US): 4.25"
Width (US): 1.688"

TECHNICAL INFORMATION

Amps: 1.5A
Volts: 120V

COUNTRY OF ORIGIN

Country Of Origin: MEXICO