

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, White

PT26352W



PlugTail™ Decorator Spec Grade Duplex
Receptacle 20amp 125volt White



features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: white
Product Series: PlugTail
Type: Receptacles
Number Of Poles: 2

Number Of Wires: 3
Style: Decorator

Listing Agencies/Third Party Information

RoH S: No
CUL Listing No: E140596
cULus: Yes
cUL Standard: UL498
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: E140596
UL Listed: Yes
UL Standard: UL498
UN SPS C: 39121406

Dimensions

Depth U S: .625"
Height U S: 3.281"
Width U S: 1.5"

Technical Information

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V
Volts A C: 125
Capacity: Duplex
Grade Type: Federal Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant