

## Hospital Grade - Extra-Hard Use (EHU) Plug, Black & Clear

PS5266XHG



Straight Blade Hospital Grade Plug, double pole and three wire, unit arrives completely ready-to-wire, cutting installation time significantly. Its nylon housing provides impact and chemical resistance. Its rugged two-piece cord grip provides more uniform cord retention and the internal dust shield keeps terminals free of contaminants. 15amp 125volt.



### features & benefits

- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### specifications

#### General Info

Color: Black

#### Listing Agencies/Third Party Information

CSA Listing Info: No  
CUL Listing No: No  
cULus: Yes  
cURus: No  
Federal Spec: Yes  
UL Listing No: No

UN SPS C: 39121402

UR: No

**Dimensions**

Depth U S: 1.752"

Height U S: 1.516"

Width U S: 1.516"

**Technical Information**

Volts A C: 125

Grade Type: Hospital

**Buy American Act Compliance**

Country of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant