



# ISOLATED GROUND HEAVY-DUTY SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, ORANGE

IG5362 | Pass & Seymour

#### **FEATURES & BENEFITS**

Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Orange



- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 #10 AWG copper or copper-clad, solid or stranded wire.
- · Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

#### **SPECIFICATIONS**

#### **GENERAL INFO**

Color: Orange Type: Receptacles Number Of Poles: 2 Number Of Wires: 3

Special Features: Isolated ground, back, side wire

Style: Duplex

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes Federal Spec: Yes UL Listing No: UL498 UL Standard: Yes UN SPSC: 39121406

UR: No

### **DIMENSIONS**

Depth (US): 0.922" Height (US): 3.281" Width (US): 1.322"

## TECHNICAL INFORMATION

Amps: 20A

NEMA Configuration Number: 5-20R

Volts: 125V Volts (AC): 125 Capacity: Duplex

Grade Type: Federal Specification

## **COUNTRY OF ORIGIN**

Country Of Origin: MEXICO