



HARD USE SPECIFICATION GRADE SWITCH, BLACK

CSB20AC3BK | [Pass & Seymour](#)

FEATURES & BENEFITS

Construction 3way Switch, Back & Side Wire, 20amp 120/277volt, Black.



- One-piece brass alloy contact arm for reliable electrical performance.
- One-piece steel strap with integral ground is plated for corrosion resistance.
- High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.
- Heavy-duty toggle bumpers for smooth and quiet operation.
- Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.
- Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.
- Cam designed for fast make with positive break action to minimize arcing and prolong switch life.
- Oversized silver alloy contacts for longer dependable switch life.
- Tri-drive terminal and mounting screws.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: Black
Duty: Hard Use
Number Of Poles: 3-way

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 111

CSA Standard: Yes
Federal Spec: Yes
UL Listing No: 20
UL Standard: Yes
UN SPSC: 39121507

DIMENSIONS

Depth (US): 1.073"
Height (US): 3.281"
Width (US): 1.320"

TECHNICAL INFORMATION

Amps: 20A
Volts: 120/277VAC
Volts (AC): 120/277
Grade Type: Specification

COUNTRY OF ORIGIN

Country Of Origin: MEXICO