



TAMPER-RESISTANT HEAVY-DUTY DECORATOR SPEC GRADE SINGLE RECEPTACLE, BACK & SIDE WIRE, 15A, 125V, WHITE

TR26261W | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Heavy-Duty Decorator Spec Grade Single Receptacle, Back & Side Wire, 15amp 125volt, White

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Dual mechanical shutter system to help prevent insertion of foreign objects.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive brass terminal screws for faster installation.
- Internal screw-pressure-plate back and side wire capability.
- Two back wire holes for additional wiring flexibility.
- Corrosion-resistant plated steel strap is locked in to face and back body to resist pulling away from the face/body assembly.
- .032 inch thick brass triple-wipe power contacts.
- Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Single Receptacles

Duty: Heavy Duty

Special Features: Tamper-Resistant,back,side wire

Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No.42
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.188"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 15A
Volts: 125V
Volts (AC): 125
Capacity: Single
Grade Type: Federal Specification

COUNTRY OF ORIGIN

Country Of Origin: MEXICO