



PLUGTAIL® TAMPER-RESISTANT HOSPITAL GRADE RECEPTACLE, BACK & SIDE WIRE, 20A, 125V, RED

PTTR8300RED | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail® Tamper-Resistant Hospital Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, Red

For detailed PlugTail® information, visit our [PlugTail Headquarters](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- **Dual mechanical shutter system** to help prevent insertion of foreign objects
- **.036 inch thick, brass, triple-wipe power contacts** for lasting retention.
- **Plated steel wrap strap design** for maximum durability and corrosion resistance.
- **No exposed terminals** create a finger safe application before, during, and after installation.
- **Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.
- **Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.
- **Pre-stripped connector leads** fasten to conductors, easier than standard pigtails
- **Auto-ground clip** assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Color: Red

Type: Receptacles

Special Features: PlugTail, Tamper-Resistant

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42

CSA Standard: Yes

CUL Listing No: E140596

cULus: Yes

Federal Spec: Yes

UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.625"
Height (US): 3.281"
Width (US): 1.5"

TECHNICAL INFORMATION

Amps: 20A
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Hospital

COUNTRY OF ORIGIN

Country Of Origin: MEXICO