



TAMPER-RESISTANT EXTRA HEAVY-DUTY SURGE PROTECTIVE DUPLEX RECEPTACLE, IVORY

TR5262ISP | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back & Side Wire, 15amp 125volt, Ivory

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Dual mechanical shutter system to help prevent insertions of foreign objects.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.
- Backed-out tri-drive steel terminal screws. Side wire capability.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory

Type: Duplex

Duty: Extra Heavy Duty

Special Features: Tamper-Resistant, Isolated Ground, Audible Alarm with LED Monitor

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: Yes
cURus: No
Federal Spec: Yes
UL Listing No: No
UN SPSC: 39121406
UR: No

DIMENSIONS

Depth (US): 1.225" (Behind Strap)
Height (US): 3.82"
Width (US): 1.750"

TECHNICAL INFORMATION

Amps: 15A
Volts: 125V
Volts (AC): 125
Grade Type: Specification

COUNTRY OF ORIGIN

Country Of Origin: CHINA