



FED SPEC GRADE USB CHARGER W/ TAMPER-RESISTANT 20A DUPLEX RECEPTACLES, GRAY

TR5362USBGRY | [Pass & Seymour](#)

FEATURES & BENEFITS

Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- **Overall 3.1A USB charging capability:** Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.
- **AC receptacles available in 15 and 20A, 125V.**
- **AC receptacles are tamper-resistant as standard**—patented shutter system prevents improper insertion of foreign objects.
- **Multiple color** options available.
- **Back and side wire terminals** accommodate #14 AWG - #10 AWG stranded and solid copper wire.
- **Stainless steel** auto-ground clips assure positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Gray

Available Colors: Black, Brown, Green, Ivory, Light Almond, Nickel, Red and White

Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42, C22.2 No. 223

CSA Standard: Yes

cULus: Yes

Federal Spec: Yes
UL Listing No: Complies with test requirements UL498, UL1310
UL Standard: Yes

DIMENSIONS

Depth (US): 1.392"
Height (US): 3.28"
Width (US): 1.693"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA