
28W77 WATERTIGHT,NEMA 4X/6P LOCKING PLUG,YELLOW

28W77 | [Pass & Seymour](#)



FEATURES & BENEFITS

Locking Watertight Plug, 30amp 3°Y 600volt, L17-30 configuration,multipoint sealing system provides environmental protection of: NEMA 4, 4X, 6, 6P & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

SPECIFICATIONS

GENERAL INFO

Color: Yellow

Type: Plug

Number Of Poles: 3

Number Of Wires: 4

Special Features: Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Diameter (US): 2.50"

Length (US): 3.11"

TECHNICAL INFORMATION

Amps: 30A

Material: Rubber
NEMA Configuration Number: L17-30
NEMA Rating: 4X/6P
Volts: 3°Y 600
Volts (AC): 3°Y 600

COUNTRY OF ORIGIN

Country Of Origin: UNITED STATES OF AMERICA