

---

## 29W77 WATERTIGHT NEMA 4X/6P LOCKING CONNECTOR, YELLOW

29W77 | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Locking Watertight Connector, 30amp 3°Y 600volt, NEMA Configuration L17-30, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.

- Thermoplastic elastomer (TPV) construction stands up to impacts, oils, chemicals, heat , and weather.
- Nickel-Plated blades and contacts for long lasting, superior corrosion resistance.
- Multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, & IP67 rated.
- Devices resist high-pressure hose down of 1,500 psi.
- Color coded sealing bushings provided for large range of cord diameters
- Large ribs on body for a superior grip when mating.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Type: Connector

Features: Watertight

Number Of Poles: 3

Number Of Wires: 4

Special Features: Watertight, NEMA

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 42M

CSA Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121403

#### CONSTRUCTION INFORMATION

Material 1: Rubber

#### DIMENSIONS

Diameter (US): 2.76"

Length (US): 4.88"

#### TECHNICAL INFORMATION

Amps: 30A

Material: Rubber

NEMA Configuration Number: L17-30

NEMA Rating: 4X/6P

Volts: 3°Y 600V

Volts (AC): 3°Y 600V

#### COUNTRY OF ORIGIN

Country Of Origin: UNITED STATES OF AMERICA