



TR26242GRY TAMPER-RESISTANT  
DECORATOR SPEC GRADE  
RECEPTACLE, SIDE WIRE ONLY, 15A, 125V,  
GRAY

TR26242GRY | [Pass & Seymour](#)

## FEATURES & BENEFITS

Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 15amp 125volt, Gray

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## SPECIFICATIONS

### GENERAL INFO

Color: Gray

Type: Receptacles

Special Features: Tamper-Resistant, side wire only

Style: Decorator

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

cUL Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

### DIMENSIONS

Depth (US): 0.65"

Height (US): 3.28"

Width (US): 1.32"

### TECHNICAL INFORMATION

Amps: 15A  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Specification

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

