



TR26242LA TAMPER-RESISTANT
DECORATOR SPEC GRADE
RECEPTACLE, SIDE WIRE ONLY, 15A, 125V,
LIGHT ALMOND

TR26242LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Decorator Spec Grade Receptacle, Side Wire Only, 15amp 125volt, Light Almond

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.

- Dual mechanical shutter system to help prevent insertions of foreign objects.
- High Impact resistant nylon face.
- Auto-ground clip assures positive ground.
- Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.
- Backed-out tri-drive steel terminal screws. Side wire only.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Type: Receptacles

Special Features: Tamper-Resistant, side wire only

Style: Decorator

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

cUL Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.65"

Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

