

Decorator 20A Half-Controlled Plug Load Duplex Receptacle, Gray

26352CHGRY



This durable, dependable Plug Load receptacle is designed to help you meet ASHRAE energy standards. The controlled marking printed on the tough nylon face is both NEMA-approved and compliant with the National Electrical Code®.



features & benefits

- NEMA approved controlled receptacle marking pad printed on the face of receptacle for superior abrasion resistance.
- CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.
- Can be used to control loads using the Wattstopper DLM system and other building control systems.
- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: Gray

Type: Plug Load Receptacle
Style: Decorator

Listing Agencies/Third Party Information

cULus: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: 0.833"
Height U S: 3.281"
Width U S: 1.322"

Technical Information

Amps: 20A
NEMA Configuration Number: 5-20R
NEMA Rating: Yes
Volts: 125V
Volts A C: 125
Grade Type: Specification

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant