

PASS & SEYMOUR®

SELF-TEST GFCI RECEPTACLES

REINVENTING SAFETY

ALL AROUND




designed to be better.™

 **legrand**®

MORE PROTECTION. MORE FUNCTIONALITY.

IN MORE ENVIRONMENTS.






SAFETY IS OUR CODE

When we invented the first GFCI receptacle, our goal was to keep people safe. Today, because of their proven effectiveness, they are required by code in numerous locations. That's why we've made it our mission to offer intelligently designed solutions for every residential and commercial environment.

Whether the jobs call for receptacles, combination devices, portable, tamper-resistant, weather-resistant, RoHS-compliant, NAFTA-compliant, hospital grade, audible alarm, or specification grade — there's a reliable P&S GFCI innovation for you.



LEGRAND

KEEPS THE INNOVATIONS COMING

At Legrand, we've been providing real solutions to real problems for so long, it's almost second nature. From the world's first GFCI receptacle in 1971, to the introduction of ground-breaking SafeLock® Protection some 30 years later, we've been delivering GFCI innovations designed to enhance safety, shorten installation times, and increase productivity for more than four decades.

Now, we've reset the bar on electrical safety again with our newest innovation: the P&S Self-Test GFCI Receptacle.

Designed to exceed UL requirements, it's **the only GFCI that tests itself every three seconds**—instead of the industry standard three hours—providing a level of reliable electrical protection that's unprecedented. The new device is also designed with a thinner profile to make more room for wires in the wall box. That means it's not only the safest GFCI receptacle out there, but the easiest to install as well.



Self-Test GFCI Technology—conducts an automatic test **EVERY THREE SECONDS**, ensuring it's always ready to protect.

Patented SafeLock® Protection — if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.

High-impact-resistant, thermoplastic construction for superior strength and durability.

Thinner profile speeds installation by leaving more room for wires in the box.

Tamper-resistant automatic shutter system prevents young children from inserting common household objects.

Meets 2015 UL requirements

FSUL Listed (Federal Specification WC596)

Ground terminal back-wire clamp for fast installation.

The most durable GFCI available. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.

The indicator light flashes if the device fails the self-test, signaling that the GFCI should be replaced.



Two back-wire holes per termination add wiring flexibility, eliminate pigtail, and save box space.

Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.

A SAFETY SOLUTION FOR EVERY HOME

IT ALL COMES DOWN TO KEEPING PEOPLE SAFE.

Our broad Pass & Seymour product line includes all the residential GFCI devices you'd expect from an industry leader, plus a number of truly innovative solutions designed to meet today's (and tomorrow's) special requirements, including:

- Spec Grade
- Tamper-Resistant
- Audible Alarm
- Combination Switch
- Combination Night Light
- Weather-Resistant
- RoHS-Compliant

TAMPER-RESISTANT NIGHT LIGHT/GFCI COMBINATION

Ensures safety and convenience

- Sealed night light with Lexan® lens prevents tampering
- LED illumination with a 20+ year life expectancy means no bulbs to change
- Photocell turns night light ON in the dark — OFF in the daylight
- Performs a self-test every 3 seconds

1597NLTTRWCC4

MAKE NIGHTTIME NAVIGATION AUTOMATIC.

Ideal for kitchens, bathrooms, hallways, stairs, nurseries, and more, this award-winning device, with built-in night light, delivers advanced safety and protection.



TAMPER-RESISTANT GFCI

Helps keep children safe

- Patented shutter system helps prevent insertion of foreign objects
- Patented SafeLock® Protection — if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected
- Meets *NEC*® requirements
- Performs a self-test every 3 seconds

1597TRW



AUDIBLE ALARM GFCI

Protection you can see and hear

- Provides an audible warning of a tripped condition and that power to a receptacle is interrupted
- Ideal for basement sump pumps and other areas where a GFCI indicator light might not be readily apparent
- Meets *NEC*® requirements
- Performs a self-test every 3 seconds

1597TRAW

ROHS-COMPLIANT GFCI

Designed to meet environmental regulations

- Meet all the requirements of the Restriction of Hazardous Substances regulations
- Provides the same functionality and protection as our traditional GFCI
- Performs a self-test every 3 seconds

1597TRRW



DECORATOR SWITCH/GFCI COMBINATION DEVICES

Ideal for remodeling

- User-preferred up-and-down switching combined with standard GFCI safety features
- Provides more functionality in single-gang opening
- Tamper-Resistant for added safety
- Ideal for bath and kitchen vent fans
- Performs a self-test every 3 seconds

1597SWTTRWCC4

INNOVATIONS THAT TRANSLATE INTO

FASTER COMMERCIAL INSTALLATIONS

SPEED AND RELIABILITY ARE THE KEY TO SUCCESSFUL COMMERCIAL INSTALLATIONS.

Our GFCIs are designed to meet those needs...and then some. That's because we've been offering GFCIs longer than anyone else, so we know what you need to do the job right the first time. Take a look at our innovative line—we think you'll find a solution that perfectly matches your needs. Every time.

Spec Grade	PlugTail®
Hospital Grade	Audible Alarm
Tamper-Resistant	Isolated Ground
Weather-Resistant	Combinations
NAFTA-Compliant	Dead Front
RoHS-Compliant	

P&S PLUGTAIL® GFCI

The fastest-installing GFCI ever. Hands down.

- Beats tough deadlines on any commercial job
- No exposed terminals creates a finger-safe application before, during, and after installation
- Available in Spec Grade, Hospital Grade, Tamper-Resistant, and LED/Night Light combinations
- Performs a self-test every 3 seconds
- Enables fast, affordable upgrades as space evolves

PT2097TRW




PlugTail's patented plug and connector design enables simultaneous, one-click termination of all terminals.



HOSPITAL GRADE GFCI

- Meets rigorous requirements of Hospital Grade supplement of UL 498
- Available in Tamper-Resistant and LED/Night Light combinations
- Performs a self-test every 3 seconds

PT2097HGTRW



SPECIFICATION GRADE GFCI

- 20 amp designed for heavy commercial use
- High-impact-resistant, thermoplastic construction for superior strength and durability
- The most durable GFCI available. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles
- Performs a self-test every 3 seconds

2097TRW



NAFTA-COMPLIANT GFCIs

Designed to meet government regulations

- GFCIs that meet the requirements of the Buy American provision of the American Recovery and Reinvestment Act
- Provides the same functionality and protection as our traditional GFCI
- Performs a self-test every 3 seconds



PORTABLE GFCIs

- Rugged polycarbonate housing stands up to impacts and hard use
- Water-resistant design for wet and corrosive indoor/outdoor environments
- Automatic reset ensures continuous power for pumps, portable signs, lights and engine heaters
- Watertight rubber cord grommets seal the GFCI from the environment

1594PC2M

Residential Self-Test GFCI Receptacles

***COLOR DESIGNATION**

I	Ivory
W	White
GRY	Gray
BK	Black
RED	Red
LA	Light Almond
NI	Nickel
—	Brown
AB	Antique Brass
DB	Dark Bronze
O	Orange

CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
1597TR*	TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI	15	125	I, W, —, BK, LA, NI, AB, DB	5-15R
1597*	TradeMaster®/Spec Grade 15 Amp Duplex GFCI	15	125	I, W, —, GRY, BK, RED, LA	5-15R
1597TRA*	TradeMaster® Audible Alarm Tamper-Resistant Duplex GFCI	15	125	I, W, —, BK, LA	5-15R
1597SWTTR*CC4	Combination Tamper-Resistant Single-Pole Switch/GFCI (No Federal Specification)	15	125	I, W, BK, LA	5-15R
1597NTLTR*CC4	Combination Tamper-Resistant 15 Amp Night Light/GFCI	15	125	I, W, BK, LA, NI, AB, DB	5-15R
1597TRWR*	TradeMaster®/Spec Grade Weather-Resistant 15 Amp Duplex GFCI	15	125	I, W, —, GRY, BK, LA	5-15R
1597TRR*	RoHS-Compliant TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI	15	125	I, W, LA	5-15R

Third-Party Compliance:

cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596

Commercial Self-Test GFCI Receptacles

CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
2097TR*	Spec Grade Tamper-Resistant 20 Amp Duplex GFCI	20	125	I, W, —, GRY, BK, RED, LA	5-20R
2097*	Spec Grade 20 Amp Duplex GFCI	20	125	I, W, —, GRY, BK, RED, LA	5-20R
1597HGTR*	Hospital Grade Tamper-Resistant Duplex GFCI	15	125	I, W, —, GRY, BK, RED, LA	5-15R
2097HGTR*		20	125		5-20R
1597HG*	Hospital Grade Duplex GFCI	15	125	I, W, GRY, BK, RED, LA	5-15R
2097HG*		20	125		I, W, —, GRY, BK, RED, LA
1597IGTR*	Spec Grade Isolated Ground Tamper-Resistant Duplex GFCI	15	125	I, W, LA, O	5-15R
2097IGTR*		20	125		I, W, GRY, BK, LA, O
1597IGHGTR*	Hospital Grade Isolated Ground Tamper-Resistant Duplex GFCI	15	125	O	5-15R
2097IGHGTR*		20	125		I, W, GRY, RED, LA, O
2097NTLTR*	Combination Tamper-Resistant 20 Amp Night Light/GFCI	20	125	I, W, GRY, LA	5-20R
1597HGNTLTR*	Hospital Grade Combination Tamper-Resistant Night Light/GFCI	15	125	I, W, —, RED	5-15R
2097HGNTLTR*		20	125		I, W, GRY, RED, LA
2097TRWR*	Spec Grade Weather-Resistant 20 Amp Duplex GFCI	20	125	I, W, —, GRY, BK, LA	5-20R

Third-Party Compliance:

cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596

Commercial Self-Test GFCI Receptacles

CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
2097TRA*	Spec Grade Audible Alarm Tamper-Resistant 20 Amp Duplex GFCI	20	125	I, W, —, GRY, BK, RED, LA	5-20R
1597HGTRA*	Hospital Grade Audible Alarm Tamper-Resistant Duplex GFCI	15	125	—, GRY, LA	5-15R
2097HGTRA*		20	125	I, W, RED, LA	5-20R
2097TRR*	RoHS-Compliant TradeMaster®/Spec Grade Tamper-Resistant 20 Amp Duplex GFCI	20	125	I	5-20R

***COLOR DESIGNATION**

I	Ivory
W	White
GRY	Gray
BK	Black
RED	Red
LA	Light Almond
NI	Nickel
—	Brown
AB	Antique Brass
DB	Dark Bronze
O	Orange

Third-Party Compliance:
cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596

Dead Front Self-Test GFCI Receptacles


CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
2087	Spec Grade Dead Front GFCI — 1-1/2 HP Motor Control Rating	20	125	I, W, BK, LA	5-20R

Third-Party Compliance:
cULus Listed, File Number E42190, Standard UL498

PlugTail® Self-Test GFCI Receptacles

CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
PT1597*	Spec Grade Duplex GFCI	15	125	I, W, GRY, LA	5-15R
PT2097*		20	125	I, W, —, GRY, BK, RED, LA	5-20R
PT1597TR*	Spec Grade Tamper-Resistant Duplex GFCI	15	125	I, W, —, GRY, BK, RED, LA	5-15R
PT2097TR*		20	125	I, W, —, GRY, RED, LA	5-20R
PT1597HG*	Hospital Grade Duplex GFCI	15	125	I, W, BK, RED, LA	5-15R
PT2097HG*		20	125	I, W, —, GRY, BK, RED, LA	5-20R
PT1597HGTR*	Hospital Grade Tamper-Resistant Duplex GFCI	15	125	I, W, BK, RED, LA	5-15R
PT2097HGTR*		20	125	I, W, GRY, BK, RED, LA	5-20R
PT2097NTLTR*	Spec Grade Tamper-Resistant Combination Night Light/GFCI	20	125	I, W	5-20R
PT1597HGNTLTR*	Hospital Grade Tamper-Resistant Combination Night Light/GFCI	15	125	I, RED	5-15R
PT2097HGNTLTR*		20	125	I, W, GRY, LA	5-20R

Third-Party Compliance:
cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596



NAFTA-Compliant Self-Test GFCI Receptacles



CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
1597TRNA*	NAFTA-Compliant TradeMaster®/ Spec Grade Tamper-Resistant Duplex GFCI	15	125	I, W, —, GRY, BK, LA	5-15R
2097TRNA*		20	125	I, W, GRY, LA	5-20R
2097NA*	NAFTA-Compliant TradeMaster®/ Spec Grade 20 Amp Duplex GFCI	20	125	I, W, —, GRY, LA, BL	5-20R
2097HGTRNA*	NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI	20	125	I, W, RED, LA	5-20R
2097HGNA*	NAFTA-Compliant Hospital Grade 20 Amp Duplex GFCI	20	125	I, W, —, GRY, RED, LA	5-20R
1597TRWRNA*	NAFTA-Compliant Tamper-Resistant Weather-Resistant Duplex GFCI	15	125	I, W, —, LA,	5-15R
2097TRWRNA*		20	125	I, W, —, GRY, LA	5-20R

*COLOR DESIGNATION

I	Ivory
W	White
GRY	Gray
BK	Black
RED	Red
LA	Light Almond
NI	Nickel
—	Brown
AB	Antique Brass
DB	Dark Bronze
O	Orange
BL	Blue

Third-Party Compliance:

cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596

NAFTA-Compliant PlugTail® Self-Test GFCI Receptacles

CATALOG NO.	DESCRIPTION	RATINGS		COLORS	NEMA Config.
		A.	V.		
PT1597NA*	NAFTA-Compliant Spec Grade Duplex GFCI	15	125	W, GRY, LA	5-15R
PT2097NA*		20	125	W, BK, LA	5-20R
PT2097TRNA*	NAFTA-Compliant Spec Grade Tamper-Resistant 20 Amp Duplex GFCI	20	125	I, W, LA	5-20R
PT2097HGNA*	NAFTA-Compliant Hospital Grade 20 Amp Duplex GFCI	20	125	I, W, GRY, RED	5-20R
PT2097HGTRNA*	NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI	20	125	I, W, GRY	5-20R
PT1597NTLTRNA*	NAFTA-Compliant Spec Grade Tamper-Resistant Combination Night Light/Duplex GFCI	15	125	W	5-15R
PT2097NTLTRNA*		20	125	I, W	5-20R
PT2097HGNTLTRNA*	NAFTA-Compliant Hospital Grade Tamper- Resistant Combination Night Light/Duplex GFCI	20	125	I	5-20R

Third-Party Compliance:

cULus Listed, File Number E42190, Standard UL498, Federal Specification WC596

©2015 Legrand BR1241 All Rights Reserved 06/15 EMA/CGXTP

designed to be better.™



Electrical Wiring Systems

P.O. Box 4822
Syracuse, NY 13221-4822
800.776.4035
www.legrand.us/PassandSeymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

For additional technical or application-specific information, call
800-223-4185 or visit our website at www.legrand.us/PassandSeymour.
We're eager to put our expertise to work for you.

FOLLOW US

