

# Decorator 15A Half-Controlled Plug Load Duplex Receptacle, Black

26252CHBK



This durable, dependable Plug Load receptacle is designed to help you meet ASHRAE energy standards. The controlled marking printed on the tough nylon face is both NEMA-approved and compliant with the National Electrical Code®.



## features & benefits

- NEMA approved controlled receptacle marking pad printed on the face of receptacle for superior abrasion resistance.
- CH versions feature a factory broken split circuit tab allowing you to control half of the receptacle.
- Can be used to control loads using the Wattstopper DLM system and other building control systems.
- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance.
- Impact-resistant nylon face.
- Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## specifications

### General Info

Color: Black

Type: Plug Load Receptacle  
Style: Decorator

### **Listing Agencies/Third Party Information**

cULus: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: UL498  
UL Standard: Yes  
UN SPS C: 39121406

### **Dimensions**

Depth U S: 0.833"  
Height U S: 3.281"  
Width U S: 1.322"

### **Technical Information**

Amps: 15A  
NEMA Configuration Number: 5-15R  
NEMA Rating: Yes  
Volts: 125V  
Volts A C: 125  
Grade Type: Specification

### **Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant