



SINGLE POLE/3-WAY SWITCH & 15A TAMPER-RESISTANT OUTLET, WHITE

RCD38TRW | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® Screwless Wall Plate not included.

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

- Part of the all-new radiant® collection.
- Unique "Up/Down" switches match the look and feel of radiant paddle switches.
- Easy-to-use oversized main switch for primary load.
- Patented Snap-In Light Module (sold separately) transforms a combination switch into an illuminated switch in seconds.
- Impact-resistant face and body.
- Full wraparound metal strap, commercial grade with lock-in tabs.
- All screws are tri-drive.
- External screw-pressure-plate back and side wired. Accepts #12 and #14 AWG.
- Single Pole/3-Way Switches can be wired as a single pole or 3-way switch.
- Largest breadth of 15 amp offering.
- Dual mechanical shutter system helps prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Combination

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: 20

UL Standard: Yes

UN SPSC: 39121704

DIMENSIONS

Depth (US): 1.43"

Height (US): 3.81"

Width (US): 1.29

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

NEMA Rating: Yes

Volts: 120/125VAC