



## COVER FOR 30A TURNLOK® WATERTIGHT RECEPTACLE

6800 | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

2.38" diameter opening to accommodate a 30A Turnlok watertight receptacle.

- Unbreakable glass-filled polycarbonate construction to withstand years of job site abuse and harsh environmental exposure.
- Stainless steel mounting screws also resist corrosion.
- Covers comply with 2005 NEC Section 406.8(A) and 406.8(B)(2).
- Molded-in label area (2.8 sq. in.) for pre-printed or handwritten labels for identification of circuits, ratings and other application data.
- WPG1 and WPG2 have lockable bullnose for OSHA locktag/tagout compliance.
- Covers fit all competitive inlets and outlets.
- Pre-attached gaskets for easy installation and tight seal to panel or weatherproof box -- with no misaligned or collapsed gaskets.
- Tamper-proof hinge features permanent, locked-in pins for added security.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black

Type: Covers

Features: Watertight

Duty: Heavy Duty

Special Features: Weatherproof

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

cULus: Yes

UL Listing No: Yes

#### DIMENSIONS

Height (US): 4.60"

Width (US): 3.00"

**TECHNICAL INFORMATION**

Material: Plastic

Capacity: 30A Receptacle

**COUNTRY OF ORIGIN**

Country Of Origin: UNITED STATES OF AMERICA