

---

## STERIGUARD™ STRAIGHT BLADE PLUG 15A, 125V

14W47AM | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

"SteriGuard™ Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers' beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure hosedown, these plugs and connectors feature multiple seals to ensure protection against the environment. SteriGuard provides a cost-effective way to add additional safety precautions and unequaled assurance that every feasible step has been taken in the interest of consumer protection."

- UL and CSA Listed
- NSF (National Sanitation Foundation) Certified
- Patent Pending
- Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
- Anti-microbial Additive Resistant to Scuffing and Cleaning
- Escherichia (E.Coli): - Log reduction > 4.8, reduced surface bacteria by > 99.99%
- Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97%
- Salmonella – Log Reduction > 3.6, reduces surface bacteria by > 99.97%
- RoHS Compliant (Non-Halogenated)
- Independently tested and Certified to JIS Z2801 standards
- Resistant to High Pressure Hose-down applications
- Tongue & Groove Environmental Sealing
- Keyed Body and Cover for Alignment
- NEMA Type 4, 4x, 6, 6P and IP67 Protection
- SteriGuard™ Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging; agriculture, pharmaceutical, and health care.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Yellow

Type: Plug

Number Of Poles: 2

Number Of Wires: 3

Special Features: Watertight

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Standard: Yes

Federal Spec: Yes

UL Listing No: E146159

UL Standard: Yes

UN SPSC: 39121402

#### DIMENSIONS

Diameter (US): 1.63"

Length (US): 2.68"

#### TECHNICAL INFORMATION

Amps: 15A

Material: Rubber

NEMA Configuration Number: 5-15P

NEMA Rating: 4X/6P

Volts: 125V

#### COUNTRY OF ORIGIN

Country Of Origin: UNITED STATES OF AMERICA