



PLUGTAIL[®] COMMERCIAL SPECIFICATION GRADE 15A USB CHARGING RECEPTACLES, WHITE

PTTR15ACUSBW | [Pass & Seymour](#)

FEATURES & BENEFITS

PlugTail[®] Commercial Specification Grade USB Charging Receptacles provide the convenience of mobile charging – without the need for a bulky AC adapter. This device is a perfect match for the constant needs of today’s mobile environment and is rugged enough to withstand hard-use commercial applications. It comes equipped with two UL Fed Spec AC receptacles and two USB charging ports for mobile devices – one Type-A port and one Type-C port for newer products. An efficient, 15.5W power supply provides ample power needed for charging mobile phones and tablets. The PlugTail termination provides a more productive, secure, and safer installation and allows you to connect with the future of wiring device innovations.

For detailed PlugTail[®] information, visit our PlugTail Headquarters.



- **AC receptacles are tamper resistant as standard** – patented shutter system prevents improper insertion of foreign objects
- **Efficient, 15.5W power supply** for fast charging of mobile phones and tablets
- **Triple-wipe, brass line contacts** for 15A commercial applications
- Multiple color options available
- **Zinc-plated steel** for corrosion resistance
- **5Vdc Type-C USB port** to charge USB Type-C compatible mobile devices
- **PlugTail termination** allows for more productive, finger-safe installation and added future flexibility
- **Stainless steel auto-ground clips** assure positive ground
- Available in 15 & 20A, Specification Grade and Hospital Grade configurations
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Color: White

Available Colors: Brown, Ivory, Light Almond, Black, Gray
Type: Duplex PlugTail Receptacles
Special Features: Type-A and Type-C USB port

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 42, C22.2 No. 225
CSA Standard: Yes
cULus: Yes
Federal Spec: Yes
UL Listing No: Complies with test requirements UL 498, UL 1312
UL Standard: Yes

DIMENSIONS

Depth (US): 1.45"
Height (US): 3.281"
Width (US): 0.69"

TECHNICAL INFORMATION

Amps: 15A
Material: Thermoplastic
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Operating Temperature (Celsius): Maximum continuous +60°C, minimum -40°C without impact
Volts: 125V

COUNTRY OF ORIGIN

Country Of Origin: MEXICO