

Conduit Knockouts





BC52151-K	CI52151-KSB
Concentric knockouts.	Concentric knockouts.





BC52151-KSSX BC53151-K

Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket.

Concentric knockouts.



Cat. No.	Volume	Features		Knockouts				
Cat. No.	(Cu. in.)	(Cu. in.)		Raised Ground Screw	1/2 in. sides	1/2 in. bottom	3/4 in. sides	3/4 in. bottom
1-1/2 in. Deep								
BC52151-K	21.0	-	yes	10	4	6	2	
CI52151-KSB	21.0	"SB"	yes	8	4	4	2	
BC52151-KSSX	21.0	"SSX"	yes	7	4	3	2	
BC53151-K	21.0	-	-	10	-	6	-	

Conduit Knockouts





BC52171-HV-KIT

BC52171-KSSXHVKIT







CI52171-1-SSX-1

CI52171-1

BC52171-K

"Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs.

With integral support bracket.
Present for 2 x 1/2 in. drywall thickness.

Concentric knockouts.









CI52171-KSB

BC52171-KSSX

BC53171-K

Concentric knockouts.

Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Present for 1 x 1/2 in. drywall thickness.

Concentric knockouts. "Wraparound" bracket for 2-1/2 in. and 3-5/8 in. steel studs. With integral support bracket. Present for 2 x 1/2 in. drywall thickness.

Concentric knockouts.



Cat. No.	Volume	Features		Knockouts					
Cat. No.	(Cu. in.)		Bracket Raised Ground Screw		1/2 in. bottom	3/4 in. sides	3/4 in. bottom	1 in. sides	
2-1/8 in. Deep									
BC52171-HV-KIT	33.6	-	yes	6	-	2	-	-	
BC52171-KSSXHVKIT	33.6	"SSX"	yes	6	-	2	-	-	
CI52171-1	30.0	-	yes	-	4	-	2	4	
CI52171-1-SSX	21.0	"SSX"	yes	-	4	-	2	2	
CI52171-1-SSX-1	21.0	"SSX"	yes	-	4	-	2	2	
BC52171-K	30.0	-	yes	10	4	6	2	-	
CI52171-KSB	30.0	"SB"	yes	8	4	4	2	-	
BC52171-KSSX	30.0	"SSX"	yes	7	4	3	2	-	
CI52171-KSSX-1	30.0	"SSX"	yes	7	4	3	2	-	
BC53171-K	30.0	-	-	10	-	6	-	-	



Covers









BC52-C-1

BC52-C-6

CI52-C-3

BC52-C-0









CI52-C-10 to CI-52-C-62

BC52-C-0-B

BC52-C-00

BC52-C-17 to Cl52-C-18-5/8




Cat. No.	Description		
Flat Covers			
BC52-C-1	Blank		
BC52-C-6	1/2 in. conduit kno	ockout	
Plaster Ring Cover			
CI52-C-3	Raised 1/2 in.	(3.4 cu. in.)	Tapped ears on 2-3/4 in. centers
Single Device Covers			
BC52-C-0	Flat		
BC52-C-0-B	Flat blank cover		
CI52-C-10	Raised 1/8 in.	(1.0 cu. in.)	
BC52-C-13	Raised 1/2 in.	(3.6 cu. in.)	
CI52-C-14	Raised 3/4 in.	(5.7 cu. in.)	
CI52-C-14-5/8	Raised 5/8 in.	(4.3 cu. in.)	
CI52-C-15	Raised 7/8 in.	(6.8 cu. in.)	
CI52-C-16	Raised 1-1/4 in.	(9.5 cu. in.)	
CI52-C-62	Raised 1/4 in.	(1.8 cu. in.)	
Two Device Covers			
BC52-C-00	Flat		
BC52-C-17	Raised 1/2 in.	(6.2 cu. in.)	
CI52-C-18	Raised 3/4 in.	(10.3 cu. in.)	
CI52-C-18-5/8	Raised 5/8 in.	(8.3 cu. in.)	





Covers







BC52C49-1/2 to Cl52-C-51-2

52 C 52 1/2 to 52 C 54 2

52CADJ



Cat. No.	Description				
One Device Square Cornered T	-				
BC52C49-1/2	Raised 1/2 in.	(3.4 cu. in.)			
BC52C49-3/4	Raised 3/4 in.	(5.3 cu. in.)			
BC52-C-49-5/8	Raised 5/8 in.	(4.3 cu. in.)			
BC52-C-49-1	Raised 1 in.	(6.8 cu. in.)			
CI52-C-49-1 1/4	Raised 1-1/4 in.	(8.6 cu. in.)			
CI52-C-50-1 1/2	Raised 1-1/2 in.	(10.0 cu. in.)			
CI52-C-51-2	Raised 2 in.	(14.0 cu. in.)			
One Device Square Cornered T	One Device Square Cornered Tile Covers - Adjustable				
52CADJ					
Two Device Square Cornered Tile Covers					
52 C 52 1/2 Raised 1/2 in. (6.0 cu. in.)					
52 C 52 5/8	Raised 5/8 in.	(8.3 cu. in.)			
52 C 52 3/4	Raised 3/4 in.	(9.0 cu. in.)			
52 C 52 1	Raised 1 in.	(12.5 cu. in.)			
52 C 52 1 1/4	Raised 1-1/4 in.	(15.5 cu. in.)			
52 C 53 1 1/2	Raised 1-1/2 in.	(19.0 cu. in.)			
52 C 54 2	Raised 2 in.	(25.5 cu. in.)			

Covers







BC8361

BC8362

BC8363









BC8364

BC8365

BC8366

BC8367



Cat. No.	Description				
3/8 in. Raised Surfac	3/8 in. Raised Surface Covers (4.6 cu. in.) Device Mount				
BC8361	One toggle switch				
BC8362	For 2-5/8 in. diameter 30 / 50 A single receptacle				
BC8363	For 1-13/32 in. diameter 15 A single receptacle				
BC8364	For 1-19/32 in. diameter 20 / 30 A single locking receptacle				
BC8365	One duplex receptacle				
BC8366	For 2-9/64 in. diameter 30 A single receptacle				
BC8367	Two toggle switches				

Complete with device mounting screws

	NEMA Configuration							
Cover	Α	V	Pole	Wire	Phase	Rec. Dia	NEMA	
BC8363	15	125	2	3	1	1.406	5-15R	
BC8364	20	125	2	3	1	1.562	L5-20R	
BC8364	20	250	2	3	1	1.562	L6-20-R	
BC8364	20	347	2	3	1	1.562	L24-20R	
BC8364	20	600	2	3	1	1.562	L9-20R	
BC8364	20	125/250	3	3	1	1.562	L10-20R	
BC8364	20	250	3	3	3	1.562	L11-20R	
BC8364	20	125/250	3	4	3	1.562	L14-20R	
BC8366	30	125	2	3	1	2.109	5-30R	
BC8364	30	125	2	3	1	1.562	L5-30R	
BC8366	30	250	2	3	1	2.109	6-30R	
BC8364	30	250	2	3	1	1.562	L6-30R	
BC8362	30	125/250	3	4	3	2.647	14-30R	
BC8362	50	125/250	3	4	1	2.647	14-50R	







Covers





Cat. No.	Description				
3/8 in. Raised Surface Covers (4.6 cu. in.)					
BC8368	2 Decora/GFCI				
BC8371	Two duplex receptacles				
BC8375	One toggle switch, one duplex receptacle				
BC8376	One Decora/GFCI				
BC8377	One toggle switch, one Decora/GFCI				
BC8378	One duplex receptacle, one Decora/GFCI				
GFCI Conversion Kits (Stainles	GFCI Conversion Kits (Stainless Steel / Steel)				
BC97002	To install GFCI on 4 in. square boxes. Complete with mounting screws				

Complete with device mounting screws
When extra capacity is required, the 8300 Series of 4 in. square covers can be mounted on a 72 Series of 4-11/16 in. square boxes using a CI72-A-52 adaptor. (see page A41)

