

CISLF-9-03



## IBERVILLE®

90 degrees skintight cord connector nylon  
3/8 in.

### General

Type:	Flexible Cord
Application:	Indoor and outdoor use
T&B UPC:	62253873209
T&B Status:	M
Degree Angle:	90 degrees
Material:	Nylon

### Dimension Information

Dia. Over Cable Jacket (max):	0.312 in.
Dia. Over Cable Jacket (min):	0.187 in.
Trade Size:	3/8 in.