

739P



marrette®

The Marrette Type II Winged wire connector is design engineered for additional twisting power to meet the high quality expectations of the electrical professional.

General

Type:	Type II Winged
T&B UPC:	06739600819
T&B Status:	M
Electrical Rating:	Approved for circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
Inner Material:	Live action variable volume spring
External Cap Features:	Long-Wing design for smooth hand application. The long, off-set wings with raised edges offer a full-length, "finger-friendly" gripping surface. Torque can be selectively applied exactly where you want it. Top - for tight finger locations, Bottom - for large wire bundles.
Inner Spring Features:	Live Action variable volume spring expands to accommodate a wide range of wire combinations.
Conductor:	Copper only
Temperature Rating:	105°C
Colour:	Blue
Material:	Tough durable polypropylene

Packaging Information

Packaging Format:	Propak
Quantity per Package:	50
Std. Pkg. (Min/Mult):	500 Units

Dimension Information

Wire Size:	14 - 6 AWG
------------	------------