

333KP



marrette®

The Marrette XTP is a high quality, twist-on wire connector with a unique spring and cap grip design that sets it apart from the competition.

General

Type:	XTP
T&B UPC:	06739633300
T&B Status:	M
Electrical Rating:	Models nos. 329 and 330 are approved for circuits up to 300 V only. Models nos. 331, 333, 335 and 822 are approved for circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
Inner Material:	Live action variable volume spring
External Cap Features:	Posi-Grip surface combines a matte finish with closely-spaced, deep grooves for superior twisting power, even when hands are greasy or damp.
Inner Spring Features:	Exclusive Live Action variable volume spring expands to accommodate more wires with less twisting effort, compared to other connectors with a "fixed spring" design.
Conductor:	Copper only
Temperature Rating:	105°C
Colour:	Yellow
Material:	Tough durable polypropylene

Packaging Information

Packaging Format:	Resealable Bag
Quantity per Package:	500
Std. Pkg. (Min/Mult):	5000 Units

Dimension Information

Wire Size:	18 - 10 AWG
------------	-------------