

31P



marrette®

The Marrette Black High Temperature rating makes it the best solution for high wattage lighting fixtures and signs.

General

Type:	Black High Temperature
T&B UPC:	06739600885
T&B Status:	M
Electrical Rating:	For circuits up to 600 V, and lighting fixtures and signs up to 1000 V.
Inner Material:	Copper-coated spring
External Cap Features:	Large, finely ribbed, "barrel-shaped" - Deep wide throat - Threaded entry
Inner Spring Features:	Conical design
Conductor:	Copper only
Temperature Rating:	150°C
Colour:	Black
Material:	Rugged thermoplastic polymer

Packaging Information

Packaging Format:	Propak
Quantity per Package:	100
Std. Pkg. (Min/Mult):	1000 Units

Dimension Information

Wire Size:	18 - 14 AWG
------------	-------------