

WPT-L

LED WALL PACK

22W or 40W (1830 or 3293 lumens)

65

cULus listed Approvals:

Suitable for outdoor use.





DESCRIPTION

The newly designed WPT-L is a highly efficient LED wall mount luminaire. This fixture is supplied with a photocell (120V) and a wall bracket (for surface mounting only). This fixture is best suited for entrances, underpasses, or anywhere controlled security lighting is required. The WPT-L is made of tough die cast aluminum housing and is IP65 rated.

TECHNICAL SPECIFICATIONS


- Die cast aluminum housing
- Integrated photocell (120V standard)
- Bronze UV resistant powder coat finish
- Input voltage: 120V AC (208-277V and 347V AC optional)
- High quality, long life LEDs
- Estimated lifespan of 50 000 hours
- 22W offers 1830 total lumens
- 40W offers 3293 total lumens
- 5000K color temperature
- Low starting temperature of -40°C

Accessories (order SEPARATELY)				
BKT522-BR	Up/Down Mounting Bracket*			
BKT526-BR	Glare Shield			

^{*} Must purchase 2x W16T-L luminaires for every 1x BKT522-BR

DIMENSIONS

Contractor:



ORDERING GUIDE

WPT -	– L	_	_	/	50K	P
Series	Lamp type	Wattage	Voltage	-	Colour temperature	Options
WPT	L - LED	S1 - 1830 lumens (22W) S2 - 3293 lumens (40W)	A - 120V (standard) G - 208-277V H - 347V		50K - 5000K	P - 120V photocell (standard in 120V and 347V) P277 - 208-277V photocell

DLC (Design-Lights Consortium®) qualified products. Please visit www.designlights.org/QPL to verify the latest update of the DLC Qualified Products List and validate which ones are qualified. Some restrictions may apply.

