

SLEXS/SLSRS

STEEL

NRCan C860 Registered

Steel Construction

LED 120/347VAC Input

SP Approvals:
 ® CSA Certified to C22.2 #141.15, C860

DESCRIPTION

The SLEXS/SLSRS series of commercial steel signs features a slim profile that eliminates light leaks combined with a simple, easy to install design. Available in AC only, AC/DC and internally self-powered versions.

CIRCUITRY - AC & AC/DC

- LED ultra bright light source
- 120/347VAC Input, field selectable
- 1.9W power consumption single or double face
- Emergency DC wattages as follows:
6VDC = 1.3W 12VDC = 1.7W 24VDC = 3.5W

CIRCUITRY - SELF-POWERED


- LED ultra bright light source
- 120/347VAC Input, field selectable
- 4W power consumption single or double face
- High-performance, sealed Ni-Cad battery
- 90 minutes emergency duration (standard)
 120 minutes emergency duration is optional
- Solid state transfer and battery charger



MECHANICAL

- 20 Gauge steel construction
- Slide out faceplates and backplates for rapid and simple installation
- Snap out directional chevrons/arrows
- Universal spider knockout pattern stamped into backplate for junction box mounting
- Universal models include ceiling or end mount, field installable canopy kit c/w spider plate
- Multiple conduit entry knockouts
- White powder coat finish standard, other finishes and colours optional

DIMENSIONS



ORDERING GUIDE

Series	Approval	Nbr of faces	Colour	DC voltage	Options†
SLEXS - Exit SLSRS - Sortie	C - C860 Certified	0 - Universal faces 1 - Single face 2 - Double faces	WH - White BK - Black GY - Grey SP - Custom colour (specify)	UDC - 6, 12, 24V universal DC NDC - AC only IB - Self powered for 90 min. IB1 - Self powered for 120 min.	TP, WG*, PG, OP, K5

†For detailed options descriptions, please consult the options page.

* Specify mounting.

QUICK SHIP: Not all products are Quick Ship. To view our Quick Ship qualified products, please consult our Quick Ship Product Guide at stanprols.com/quick-ship-product-guide. Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.