

SLEXX/SLSRX

EXTRUDED ALUMINUM

NRCan C860 Registered LED 120/347VAC Input



Approvals:

CSA Certified to C22.2 #141.15, C860

Energy Verified Énergie Vérifiée

DESCRIPTION

The clean lines of the SLEXX/SLSRX series of commercial extruded aluminum signs present a fully modern appearance. The extruded aluminum provides for a rigid, durable and lightweight sign. Available in AC only, AC/DC and internally self-powered versions.

CIRCUITRY - AC & AC/DC

- LED ultra bright light source
- 120/347VAC Input, field selectable
- 1.9W power consumption single or double face
- Emergency DC wattages as follows:

EXIT: 6VDC = 1.0W **12VDC** = 1.4W **24VDC** = 3.5W **SORTIE: 6VDC** = 1.3W **12VDC** = 1.7W **24VDC** = 3.2W

CIRCUITRY - SELF-POWERED

- LED ultra bright light source
- 120/347VAC Input, field selectable
- 4W power consumption single or double face
- High-performance, sealed Ni-Cad battery
- 90 minutes emergency duration (standard)
 120 minutes emergency duration is optional
- Solid state transfer and battery charger





quic

MECHANICAL

- Extruded aluminum construction
- Slide in/out captive faceplate(s) and backplate for rapid and simplified installation
- Snap out directional chevrons/arrows
- Universal spider knockout pattern stamped into backplate for junction box mounting
- Universal models include ceiling or end mount, field installable canopy kit c/w spider plate
- White powder coat finish standard, other finishes and colours optional

DIMENSIONS

5.63"	4.38" 0.38"	5.63"
«SORTIE	≫	« EXIT »
18.5"		13"

ORDERING GUIDE

	C		_	-	
Series	Approval	Nbr of faces	Colour	DC Voltage	Options†
SLEXX- (Exit) SLSRX -(Sortie)	C - C860 Certified	2 - Double face	WH - White BK - Black GY - Grey BA - Brushed aluminum SP - Custom colour (specify)	NDC - AC only UDC - 6, 12, 24V universal DC IB - Self powered for 90 min. IB1 - Self powered for 120 min.	VS, WG*, LG, OP, K5

[†] For detailed options descriptions, please consult the options page

QUICK SHIP: Not all products are Quick Ship. To view our Quick Ship qualified products, please consult our Quick Ship Product Guide at stanprols.com/quick-ship-product-guide. Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.



^{*} Specify mounting.