

YAL27T12 : CANLUG-3/0 STR-
SHORT-1/2



Experience. Technology. Answers.™

www.burndy.com

BURNDY® PRODUCTS

Specifications

Dimensional	
Tongue Angle	Straight
Length (in)	2.22
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Standard
Thickness	0.13
B Length (in)	0.79
Pad Width (in)	0.91
Other Features	
UPC	78181041703
General	
Number of Holes	1
Conductor(s)	
Copper Stranded (Range)	3/0
Copper Solid Size (Range)	N/A
Physical	
Type of Plating	Tin - Electro Plated
Color Code	Orange
Plated (Yes or No)	Y
Index Number	14
Product Material	Copper
Approvals / Certifications	
Industry Standards	UL468A -468B
UL Listed	Yes Y
CSA Certified	Yes Y
ROHS Compatible	Compliant
UL Recognized	N