



## Features/Benefits

- ALTO® Lamp Technology Passes EPA's TCLP test for non-hazardous waste.
- Utilizes amalgam technology to provide > 90% of rated lumens in ambient temperatures from 23F to 130F.
- Triple tube design available in 18, 26, 32, and 42W.
- Excellent Color Rendering 82 Color Rendering Index (CRI).
- Broad Range of Color Temperature Available in 2700, 3000, 3500 and 4100K.
- Dimmable PL-T 4-pin lamps may be used with electronic dimming ballasts.
- Long Life 12,000 hours.
- Energy Saving Designed for use with electronic ballasts for lower operating costs and flicker-free starting.

## **Applications**

· Ideal for downlights and medium bay multi-lamp fixtures for general lighting.

## Notes

- Rated average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently. (202)
- Approximate Initial Lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life, when the output is measured during operation on a reference ballast under standard laboratory conditions. (203)
- Design Lumens are the approximate lamp lumen output at 40% of the lamp's Rated Average Life. This output is based upon measurements obtained during lamp operation on a reference ballast under standard laboratory conditions. (208)

268201	
200201	
PL-T 18W/835 GX24q-2 /4P 1CT	
268201	
1 Lamp in a Folding Carton	
1	
12	
046677268206	
	268201 1 Lamp in a Folding Carton 1 12





Product data		
Case Bar Code	50046677268201	
Successor Product number		
Base	GX24q-2	
Base Information	4P	
Execution	/4P [4 Pins]	
Packing Type	1CT [1 Lamp in a Folding Carton]	
Packing Configuration	12	
Avg. Hrs. Life	16000 hr	
Ordering Code	PL-T 18W/835/4P/ALTO	
Pack UPC	046677268206	
Case Bar Code	50046677268201	
Watts	18W	
Lamp Voltage	100 V	
Dimmable	Yes	
Color Code	835 [CCT of 3500K]	
Color Rendering Index	82 Ra8	
Color Designation	White	
Color Description	835 White	
Color Temperature	3500 K	
Initial Lumens	1200 Lm	
Initial Lumens	1130 Lm	
Overall Length C	116.4 mm	
Diameter D	39.85 mm	
Diameter D1	39.65 mm	
Product Number	268201	






PL-T 18W






Base GX24q-2



PL-T/835



PL-T/835

