



Timer Controls: Analog/Mechanical Time Switches

T1975HDR | 24-Hour Heavy-Duty Time Switch



T1975HDR

24-HOUR HEAVY-DUTY TIME SWITCH

These heavy-duty time switches are designed to handle the toughest environments and have fully encapsulated motors to prevent dust or debris from entering the motor. The ON/OFF trippers are permanently attached to the metal dial to avoid the accidental loss of a tripper. These time switches offer 15-minute intervals, providing up to 96 operations each day.



Features & Applications

Features

Applications

- Oil Well Pumps

- Heavy-duty metal dial and metal enclosure withstands the most punishing environmental conditions
- Models with skipper wheel allow for operations to be omitted on selected days of the week
- Easy-to-set trippers rotate in/out for fast, accurate setting
- Up to 96 operations (48 ON/48 OFF) every 24 hours
- 15-minute intervals between events
- Fully encapsulated motor with protected gears
- Silo Unloaders
- Process Equipment
- Harsh Environment Electrical Loads
- Electrical Pumps
- Motors

Specifications

Minimum ON/OFF Times 15-min	Maximum Power Consumption (W) 3 W	Product Height (in) 10.125
Maximum ON/OFF Operations 48	Operating Temperature Max (°C) 54	Product Height (mm) 257.2
Input Voltages Display 125 VAC, 60 Hz	Operating Temperature Max (F) 130	Product Width (in) 6.5
Operation Mode 24-hours	Operating Temperature Min (°C) -40	Product Width (mm) 165.1
Has Override Switch No	Operating Temperature Min (F) -40	Product Depth (in) 3.625
Resistive 20 A, 125-480 VAC, 60 Hz	Operating Temperature Min (F) -40	Product Depth (mm) 92.1
Motor 1 HP, 250 VAC, 60 Hz 1/2 HP, 125 VAC, 60 Hz	Wire Size Max #12 AWG	Warranty 1-year
	Enclosure Type Outdoor Type 3R Metal	

Related Accessories and Parts (3)

22T338GR

**MOUNTING BRACKET FOR INTERMATIC
STANDARDIZED TIMER MECHANISMS**

156T1950A

**SET OF 12 TRIPPERS FOR T1900, T2000,
C8800, R8800 AND T8800 SERIES**

156T1950AD12

**12 BAGS OF 156T1950A TRIPPERS FOR
T1900, T2000, C8800, R8800, AND T8800
SERIES**

Copyright © 2017 Intermatic Incorporated. All rights reserved.