

# Safety Switches

**SELECTION**

## Heavy Duty 600 Volt



SAFETY SWITCHES

System	Ampere Rating	Indoor - Type 1			Outdoor - Type 3R			Horsepower Ratings							
		Catalog Number	Ship. Wgt.	List Price	Catalog Number	Ship. Wgt.	List Price	240 Volt		480 Volt		600 Volt		250V DC	600V DC
								1-Phase	3-Phase	1-Phase	3-Phase	1-Phase	3-Phase		

### 600 Volt Non-Fusible<sup>①</sup>

#### 2-Pole <sup>③</sup>

#### 480 Volt AC / 600 Volt AC / 600 Volt DC

	30	HNFC261	12	-	HNFC261R	13	-	—	—	7 1/2	—	10	—	5	15
	60	HNFC262	19	-	HNFC262R	20	-	—	—	20	—	25	—	10	30
	100	HNFC263	24	-	HNFC263R	25	-	—	—	30	—	40	—	20	50
	400	HNFC265	109	-	HNFC265R	113	-	15	—	50	—	50	—	40	50
	600	HNFC266	111	-	HNFC266R	115	-	15	—	50	—	50	—	50	50

#### 3-Pole

#### 480 Volt AC / 600 Volt AC / 250 Volt DC

	30	HNFC361	12	-	HNFC361R	13	-	5	10	7 1/2	20	10	30	5	—
	60	HNFC362H <sup>②</sup>	11	-	HNFC362RH <sup>②</sup>	11	-	10	20	20	50	20	40	10	—
	60	HNFC362 <sup>①</sup>	18	-	HNFC362R <sup>①</sup>	19	-	10	20	20	50	25	60	10	25
	100	HNFC363 <sup>①</sup>	23	-	HNFC363R <sup>①</sup>	24	-	15	40	30	75	40	100	20	25
	200	HNFC364 <sup>①</sup>	46	-	HNFC364R <sup>①</sup>	47	-	15	60	50	125	50	150	40	50
	400	HNFC365	114	-	HNFC365R	118	-	15	125	50	250	50	350	50	—
	600	HNFC366	116	-	HNFC366R	120	-	15	200	50	400	50	500	50	—
	800	HNFC367	302	-	HNFC367R	305	-	15	250	50	500	50	500	50	—
1200	HNFC368	305	-	HNFC368R	307	-	15	250	50	500	50	500	50	—	

### 600 Volt Non-Fusible<sup>①</sup>

#### 2-Pole <sup>③</sup>

#### 480 Volt AC / 600 Volt AC / 600 Volt DC

		Type 4 / 4X Stainless			Type 12 Industrial <sup>⑤</sup>										
		Cat. No.	Ship. Wgt.	List Price	Cat. No.	Ship. Wgt.	List Price								
	30	HNFC261S	13	-	HNFC261J	13	-	—	—	7 1/2	—	10	—	5	15
	60	HNFC262S	20	-	HNFC262J	20	-	—	—	20	—	25	—	10	30
	100	HNFC263S	25	-	HNFC263J	25	-	—	—	30	—	40	—	20	50
	400	HNFC265S	113	-	HNFC265J	114	-	15	—	50	—	—	—	40	50
	600	HNFC266S	115	-	HNFC266J	120	-	15	—	50	—	—	—	50	50

#### 3-Pole

#### 480 Volt AC / 600 Volt AC / 250 Volt DC

	30	HNFC361S	13	-	HNFC361J	13	-	5	10	7 1/2	20	10	30	5	—
	60	HNFC362SH <sup>②</sup>	15	-	HNFC362JH <sup>②</sup>	14	-	10	20	20	50	20	40	10	—
	60	HNFC362S <sup>①</sup>	19	-	HNFC362J <sup>①</sup>	19	-	10	20	20	50	25	60	10	25
	100	HNFC363S <sup>①</sup>	24	-	HNFC363J <sup>①</sup>	24	-	15	40	30	75	40	100	20	25
	200	HNFC364S <sup>①</sup>	47	-	HNFC364J <sup>①</sup>	47	-	15	60	50	125	50	150	40	50
	400	HNFC365S	118	-	HNFC365J	119	-	15	125	50	250	50	350	50	50
	600	HNFC366S	120	-	HNFC366J	120	-	15	200	50	400	50	500	50	50
	800	HNFC367S	302	-	HNFC367J	302	-	15	250	50	500	50	500	50	50
1200	-	-	-	HNFC368J	310	-	15	250	50	500	50	500	50	50	

<sup>①</sup>Also rated 600V DC.

<sup>②</sup>Compact switch (11.1"H, 6.6"W box less cover and handle). Short circuit withstand rating—100,000 RMS sym. amps.

<sup>③</sup>Use 3-Pole switch for 200A application.

<sup>④</sup>Suitable for use as service entrance equipment.

<sup>⑤</sup>Also rated type 3S / 3R.

■ Please contact factory for availability.