

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130112-0105](#)  
**Status:** **Active**  
**Overview:** [Lighting Accessories](#)  
**Description:** 100W Guard Quick-Open with Reflector, Zinc Plated

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Portable Lighting
Series	<a href="#">130112</a>
NEMA Configuration	N/A
Outlet	None
Overview	<a href="#">Lighting Accessories</a>
Product Name	Woodhead®
Type	Accessory
UPC	78678860842
Woodhead	Yes

**Physical**

Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	No
Guard Type	Quick Open
Height	N/A
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Net Weight	195.950/g
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	N/A
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

**Material Info**

Old Part Number	1166
-----------------	------

**EU RoHS**

**ELV and RoHS**

**Compliant**

**REACH SVHC**

**Not Reviewed**

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130112Series](#)